

# Lembar data produk

Spesifikasi



## NSYTR end cover for screw single-level terminal block 1x1 - 2.5 to 10mm²

NSYTRAC22

### Main

|                                    |                                                                                                                                                                                                                     |
|------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Range                              | Lineryg                                                                                                                                                                                                             |
| Product Name                       | Lineryg TR                                                                                                                                                                                                          |
| Product Or Component Type          | Cover plate                                                                                                                                                                                                         |
| Device Short Name                  | TRA                                                                                                                                                                                                                 |
| Accessory / Separate Part Category | Insulation accessory                                                                                                                                                                                                |
| Product Compatibility              | TRV screw terminal - passthrough terminal block, length = 47.7 mm<br>TRV screw terminal - protective earth terminal block, length = 47.7 mm<br>TRV screw terminal - blade disconnect terminal block, length = 55 mm |
| Thickness                          | 2.2 mm                                                                                                                                                                                                              |

### Complementary

|                             |                                     |
|-----------------------------|-------------------------------------|
| Cable Cross Section         | 6 mm²<br>2.5 mm²<br>4 mm²<br>10 mm² |
| Number Of Connections       | 2                                   |
| Number Of Measurement Input | 2<br>1                              |
| Quantity Per Set            | Set of 50                           |
| Net Weight                  | 2.4 g                               |
| Colour                      | Grey                                |

### Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type Of Package 1       | PCE       |
| Number Of Units In Package 1 | 1         |
| Package 1 Height             | 0.400 cm  |
| Package 1 Width              | 4.000 cm  |
| Package 1 Length             | 4.700 cm  |
| Package 1 Weight             | 2.000 g   |
| Unit Type Of Package 2       | BB1       |
| Number Of Units In Package 2 | 50        |
| Package 2 Height             | 3.000 cm  |
| Package 2 Width              | 13.000 cm |
| Package 2 Length             | 17.000 cm |

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

|                              |           |
|------------------------------|-----------|
| Package 2 Weight             | 127.000 g |
| Unit Type Of Package 3       | S04       |
| Number Of Units In Package 3 | 3600      |
| Package 3 Height             | 30.000 cm |
| Package 3 Width              | 40.000 cm |
| Package 3 Length             | 60.000 cm |
| Package 3 Weight             | 9.950 kg  |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 12 months |
|----------|-----------|

## Keberlanjutan

**Green Premium™** label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO<sub>2</sub>.

**Panduan untuk menilai keberlanjutan produk** adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)

## Kinerja kesejahteraan

|                                                                                    |                                    |     |
|------------------------------------------------------------------------------------|------------------------------------|-----|
|   | Reach Free Of Svhc                 |     |
|   | Toxic Heavy Metal Free             |     |
|   | Mercury Free                       |     |
|   | Rohs Exemption Information         | Yes |
|  | Halogen Free Plastic Parts Product |     |

|                       |                                                                                                             |
|-----------------------|-------------------------------------------------------------------------------------------------------------|
| Reach Regulation      | <a href="#">REACH Declaration</a>                                                                           |
| Eu Rohs Directive     | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a>           |
| China Rohs Regulation | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope) |