

Lembar data produk

Spesifikasi



HMI encl. Spacial S3CM.
H300xW300xD200IP54 IK10,
RAL7035.Rear door.

NSYS3CM303020

Main

Range	Spacial
Product Name	Spacial S3CM
Application	Human-machine dialogue application
Category	Control enclosure
Enclosure Nominal Height	300 mm
Enclosure Nominal Width	300 mm
Enclosure Nominal Depth	200 mm
Installation Accessory Type	Suspension system
Product Destination	Interface
Device Composition	1 body 1 door with lock 2 rail 1 reinforcement plate 1 trim frame

Complementary

Body Type	Single piece body
Door Type	Plain
Number Of Doors	Rear: 1 door(s)
Door Opening Side	Reversible (120 °)
Lock Type	3 mm double-bar lock
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	Without gland plate
Accessibility For Operation	Rear
Removable Parts	Door by hinges Trim frame by screws 2 rails by screws
Material	Enclosure and front face: steel Trim frame: aluminium
Surface Finish	Epoxy-polyester powder
Colour	Enclosure: grey (RAL 7035) Front face: grey (RAL 7040)
Net Weight	7.444 kg

Environment

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Ip Degree Of Protection	IP54 conforming to IEC 60529
Ik Degree Of Protection	IK10 conforming to IEC 62262

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	32.0 cm
Package 1 Width	32.0 cm
Package 1 Length	22.0 cm
Package 1 Weight	7.444 kg

Contractual warranty

Warranty	18 months
----------	-----------

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi RoHS/REACH

Kinerja kesejahteraan

 Mercury Free

 Rohs Exemption Information [Yes](#)

Sertifikasi & Standar

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations