

Lembar data produk

Spesifikasi



Rectangular perforated mounting plate for control desk W600mm - H675xW508mm

NSYTMP6760

⚠ Telah dihentikan pada: 9 Sep 2020

⚠ Dihentikan

Main

Range	Spacial
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	Mounting plate
Device Application	Multi-purpose
Enclosure Nominal Dimensions	-
Mounting Location	On adjustment rails
Mounting Plate Description	Telequick perforated
Range Compatibility	Spacial Spacial SD
Quantity Per Set	Set of 1
Material	Steel
Surface Finish	Zinc coated

Complementary

Fixing Mode	By screws - screw type M3 - slot location By screws - screw type M6 - slot location By fixing element - fixing bracket location
Height	650 mm
Width	600 mm nominal: 450 mm real:
Thickness	2 mm
Cut-Out Dimensions	11 x 26 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3 cm
Package 1 Width	51 cm
Package 1 Length	68 cm
Package 1 Weight	3.2 kg

Contractual warranty

Warranty	18 months
----------	-----------

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi RoHS/REACH

Kinerja kesejahteraan

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Sertifikasi & Standar

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations