


Lembar data produk

Spesifikasi



NSYTR end stop with screw 9,5 mm for DIN rails 35mm

NSYTRAABV35

Main

Range	Linergy
Product Name	TR
Product Or Component Type	End stop
Device Short Name	TRA
Accessory / Separate Part Category	Mounting accessory
Product Compatibility	TRV screw terminal terminal block TRP push-in terminal block TRR spring terminal terminal block TRH IDC terminal block
Length	50.5 mm
Thickness	9.5 mm

Complementary

Mounting Mode	By screws
Quantity Per Set	Set of 50
Net Weight	14.8 g
Colour	Grey

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.950 cm
Package 1 Width	3.300 cm
Package 1 Length	4.900 cm
Package 1 Weight	14.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	50
Package 2 Height	3.700 cm
Package 2 Width	10.500 cm
Package 2 Length	24.500 cm
Package 2 Weight	716.000 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	1150

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	16.960 kg

Contractual warranty

Warranty	12 months
----------	-----------

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)

Kinerja kesejahteraan

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
	Halogen Free Plastic Parts Product	
Reach Regulation		REACH Declaration
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)