

Main

| Range | Prisma |
|---------------------------|---|
| Range Of Product | Prisma G |
| Product Or Component Type | Door |
| Range Compatibility | Prisma Prisma G duct |
| Provided Equipment | door handle keylock (key 405) other keylock and insert to be ordered separately 3 hinge |
| Type Of Door | Transparent |
| Ip Degree Of Protection | IP43 with door, canopy and IP43 gasket IP30 without door IP40 with door IP41 with door and canopy |

Complementary

| Installation Description | Floor-standing duct - width 300 mm |
|------------------------------------|--|
| Door Opening Side | Reversible |
| Number Of Locks | 3 |
| Door Opening Angle | 130 ° |
| Number Of Vertical Modules [50 Mm] | 33 |
| Enclosure Material | Handle: polyamide Glass Cover frame: treated sheet steel |
| Quantity Per Set | Set of 1 |
| Height | 1830 mm |
| Width | 300 mm |
| Depth | 36 mm |
| Net Weight | 7.12 kg |
| Material | Glass |
| Surface Finish | Matt Smooth |
| Colour | White (RAL 9001) |

Environment

| Ik Degree Of Protection | IK08 conforming to EN/IEC 62262 |
|-------------------------|--|
| Standards | IEC 61439-2 |
| | IEC 61439-1 |
| Protective Treatment | Electrophoresis treatment and hot-polymerised polyester epoxy powder |
| Packing Units | |
| | |

| • | |
|------------------------------|------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 6.500 cm |
| Package 1 Width | 33.000 cm |
| Package 1 Length | 171.500 cm |
| Package 1 Weight | 7.120 kg |
| Unit Type Of Package 2 | PAL |
| Number Of Units In Package 2 | 15 |
| Package 2 Height | 47.500 cm |
| Package 2 Width | 200.000 cm |
| Package 2 Length | 120.000 cm |
| Package 2 Weight | 106.800 kg |



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
|--------------------------|---|
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |