

Lembar data produk

Spesifikasi



partition plate, Linergy TR terminals blocks, 4point, 2mm width, for screw terminal, grey

NSYTRAP24

⚠ Telah dihentikan pada: 9 Okt 2023

⚠ Dihentikan

Main

Range	Linergy
Product Name	Linergy TR
Product Or Component Type	Partition
Device Short Name	TRA
Accessory / Separate Part Category	Insulation accessory
Product Compatibility	TRV screw terminal terminal block, length = 65.4 mm
Thickness	2 mm

Complementary

Cable Cross Section	4 mm ²
Number Of Connections	4
Number Of Measurement Input	2
Quantity Per Set	Set of 50
Net Weight	6 g
Colour	Grey

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.0 cm
Package 1 Width	15.0 cm
Package 1 Length	17.0 cm
Package 1 Weight	6.0 g
Unit Type Of Package 2	BAG
Number Of Units In Package 2	50
Package 2 Height	5.0 cm
Package 2 Width	15.0 cm
Package 2 Length	17.0 cm
Package 2 Weight	310.0 g

Contractual warranty

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Warranty

18 months

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)

Kinerja kesejahteraan

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
	Halogen Free Plastic Parts Product	

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)