



Main

Range	Linery
Product name	Linery TR
Product or component type	Terminal block
Device short name	TRR
Terminal block type	Blade disconnect
Terminal block level	1
Mounting mode	Clip-on
Nominal cross section	2.5 mm ²
Length	72 mm
Colour	Grey
Quantity per set	Set of 50

Complementary

Width	5.2 mm
Height	36.5 mm
Connections - terminals	1 x spring terminal : upstream 2 x spring terminal : downstream
Number of connections	3
Connection position	Top
Number of measurement input	2
Cable cross section	0.08...2.5 mm ² , flexible without 0.8...4 mm ² , solid
Wire stripping length	10 mm
Tool type	Connection : flat screwdriver Disconnection : flat screwdriver
[Ue] rated operational voltage	300 V CSA 600 V cURus 400 V conforming to EN/IEC 60947-7-1
[In] rated current	20 A conforming to EN/IEC 60947-7-1

	16 A CSA 16 A cURus
Material	Polyamide 6/6 (insulating case)
Dielectric loss	0.01 at 1 MHz conforming to IEC 60250 0.01 at 1 MHz conforming to VDE 0303-T4
Dielectric constant	3.7 at 1 MHz
Resistivity	10000 MΩ.m MΩ.m conforming to IEC 60093 10000 MΩ.m MΩ.m conforming to VDE 0303-T30
Surface resistance	1000 GΩ GΩ conforming to IEC 60093 1000 GΩ GΩ conforming to VDE 0303-T30
Creep resistance	500 CTI (> 400 kB) conforming to IEC 60093 500 CTI (> 400 kB) conforming to VDE 0303-T30
Flame retardance	V0, thickness 0.8 mm conforming to UL 94
Product weight	9.1 g
Range compatibility	Prisma - G Prisma - P Prisma - PH Prisma - Pack Spacial Kaedra TeSys
Product compatibility	Spacial enclosures

Environment

Product certifications	CSA cURus EAC
Dielectric strength	1000 V conforming to IEC 60243-1
Ambient air temperature for operation	-40...130 °C conforming to IEC 60216-1 -40...130 °C conforming to VDE 0304-T21

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1052 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations