

Lembar data produk

Spesifikasi



socket RUZ - mixed contact - 10 A
- < 250 V - connector - for relay
RUMC2..

RUZC2M

Main

Range Of Product	Harmony Electromechanical Relays Harmony Timer Relays
Device Short Name	RUZ
Product Or Component Type	Socket
Product Compatibility	Plug-in relay RUM with 2 C/O contact Plug-in relay RE48 with 2 C/O contact Plug-in relay RE48 with 1 C/O + 1 C/O contact
Contacts Type And Composition	2 C/O
[Ith] Conventional Free Air Thermal Current	10 A
[Ue] Rated Operational Voltage	< 250 V

Complementary

Shape Of Pin	Cylindrical
Contact Terminal Arrangement	Mixed
Connections - Terminals	Connector, 1 x 0.25...1 x 2.5 mm ² (AWG 22...AWG 14) flexible with cable end Connector, 2 x 0.25...2 x 1 mm ² (AWG 22...AWG 17) flexible with cable end Connector, 1 x 0.5...1 x 2.5 mm ² (AWG 20...AWG 14) solid without cable end Connector, 2 x 0.5...2 x 1.5 mm ² (AWG 20...AWG 16) solid without cable end
Tightening Torque	< 1 N.m for M3.5 screw(s)
Fixing Mode	By screw (panel) Clip-on (35 mm symmetrical DIN rail)
[Uimp] Rated Impulse Withstand Voltage	4 kV
Overvoltage Category	III
Pollution Degree	3
Sale Per Indivisible Quantity	10
Width	38 mm
Net Weight	0.054 kg

Environment

Ip Degree Of Protection	IP20 conforming to IEC 60529
Standards	IEC 61984
Product Certifications	UL CSA
Marking	CE
Ambient Air Temperature For Storage	-40...85 °C

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Ambient Air Temperature For Operation	-40...55 °C
---------------------------------------	-------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.84 cm
Package 1 Width	0.86 cm
Package 1 Length	1.46 cm
Package 1 Weight	0.005 kg
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	8.4 cm
Package 2 Width	8.6 cm
Package 2 Length	14.6 cm
Package 2 Weight	629.0 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	200
Package 3 Height	28.5 cm
Package 3 Width	29.9 cm
Package 3 Length	39.8 cm
Package 3 Weight	12.58 kg

Contractual warranty

Warranty	12 months
----------	-----------

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi RoHS/REACH

Kinerja kesejahteraan


 Reach Free Of Svhc	
 Toxic Heavy Metal Free	
 Mercury Free	
 Rohs Exemption Information	Yes

Sertifikasi & Standar

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations

Dimensions Drawings


Dimensions



- (1) Relays
- (2) Protection module
- (3) Maintaining clamp

Connections and Schema


Wiring Diagram



Symbols shown in blue correspond to Nema marking.

Bus Jumpers Mounting on Sockets with Separate Contacts

Example of RUZS2 bus jumper mounting on sockets (view from below)



- (1) 2 bus jumpers (polarity A2)
- (2) 2 bus jumpers (polarity A1)