

Lembar data produk

Spesifikasi



Electronic Alarm NPN Black

XVS72BMBN

Main

Range Of Product	Harmony XVS
Product Or Component Type	Electronic alarm
Device Short Name	XVS

Complementary

Colour	Black
Material	ABS (acrylonitrile butadiene-styrene): body PC (polycarbonate): terminal cover
Marking	CE
Overvoltage Category	Class II conforming to IEC 61140
Mounting Support	72 mm DIN rail
[Us] Rated Supply Voltage	12...24 V DC
[Uimp] Rated Impulse Withstand Voltage	0.8 kV
Current Consumption	117 mA at 12 V 125 mA at 24 V 158 mA at 12 V 200 mA at 24 V
Clamping Connection Capacity	<= 1 x 1.5 mm ²
Width	72 mm
Height	72 mm
Depth	69.3 mm
Net Weight	0.18 kg

Environment

Discrete Output Type	NPN
Signalling Type	16 tones alarm
Standards	UL 464 IEC 61000-6-3 IEC 61000-6-2
Product Certifications	UR
Protective Treatment	TC
Ambient Air Temperature For Storage	-35...70 °C
Ambient Air Temperature For Operation	-10...50 °C
Ip Degree Of Protection	Panel mounted: IP54 conforming to IEC 60529

Disklaimer: Dokumentasi ini tidak ditujukan sebagai pengganti dan tidak untuk digunakan untuk menentukan kesesuaian atau keandalan produk ini untuk aplikasi pengguna

Noise Level	0...90 dB (continuous or intermittent tone) at 1 m
-------------	--

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.4 cm
Package 1 Width	9.4 cm
Package 1 Length	10.41 cm
Package 1 Weight	0.27 kg
Unit Type Of Package 2	S03
Number Of Units In Package 2	16
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	5.118 kg
Unit Type Of Package 3	PAL
Number Of Units In Package 3	128
Package 3 Height	60 cm
Package 3 Width	80 cm
Package 3 Length	128 cm
Package 3 Weight	34.56 kg

Contractual warranty

Warranty	18 months
----------	-----------

Keberlanjutan

Green Premium™ label adalah komitmen Schneider Electric untuk memberikan produk dengan performa lingkungan terbaik di kelasnya. Green Premium menjanjikan kepatuhan pada peraturan terbaru, transparansi pada dampak lingkungan, serta produk melingkar dan rendah CO₂.

Panduan untuk menilai keberlanjutan produk adalah laporan resmi yang menjelaskan standar label lingkungan global dan bagaimana menafsirkan deklarasi lingkungan.

[Pelajari lebih lanjut tentang Green Premium >](#)

[Panduan untuk menilai keberlanjutan produk >](#)



Transparansi RoHS/REACH

Kinerja kesejahteraan

 Mercury Free

 Rohs Exemption Information [Yes](#)

Sertifikasi & Standar

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)

China Rohs Regulation [China RoHS declaration](#)

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)

Dimensions Drawings

Electronic Alarm

Dimensions

