Disclaimer. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product datasheet

Specifications





IP30 transparent door, W = 650 mm

08536

- ! Discontinued on: 15 Jun 2023
- ! End-of-service on: 1 Jan 2024

! Discontinued

Main

Range	Prisma
Range Of Product	Prisma P
Product Or Component Type	Door
Range Compatibility	Prisma Prisma P cubicle
Provided Equipment	door handle keylock (key 405) other keylock and insert to be ordered separately 2 hinge
Enclosure Mounting	Floor-standing
Type Of Door	Transparent
Ip Degree Of Protection	IP30

Complementary

Installation Description	Cubicle - width 650 mm
Door Opening Side	Reversible
Number Of Locks	2
Door Opening Angle	120 °
Number Of Vertical Modules [50 Mm]	36
Enclosure Material	Glass Treated sheet steel
Quantity Per Set	Set of 1
Height	2000 mm
Width	650 mm
Net Weight	18 kg
Surface Finish	Smooth Matt
Colour	White (RAL 9001)

Environment

Ik Degree Of Protection	IK08 conforming to EN/IEC 62262
Standards	IEC 61439-1 IEC 61439-2
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder

26 Apr 2024 Life Is On Schneider

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.0 cm
Package 1 Width	66.0 cm
Package 1 Length	203.5 cm
Package 1 Weight	16.95 kg
Unit Type Of Package 2	P2M
Number Of Units In Package 2	10
Package 2 Height	95.0 cm
Package 2 Width	120.0 cm
Package 2 Length	200.0 cm
Package 2 Weight	180.0 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information