



Plug outlet, Linergy HK, 2P, 16A, 1 point, 2.5mm², cable length 200

AK5PC12PH

Main

Range	Linergy
Product Name	нк
Product Or Component Type	Plug outlet
Poles Description	2P
[Ith] Conventional Free Air Thermal Current	16 A
I ² T On Activation	100000 A².s
Number Of Points	1
Number Of Cables	2 cable(s) 2.5 mm²
Cable Length	0.2 m
Quantity Per Set	Set of 6

Complementary

[Ui] Rated Insulation Voltage	600 V conforming to CSA 600 V conforming to UL 690 V conforming to IEC 60439-1
Peak Current	25 kA
Width	18 mm
Height	46 mm
Depth	38 mm
Net Weight	0.035 kg

Environment

Standards	IEC 60439	
Product Certifications	DNV UL	
	LROS (Lloyds register of shipping)	
	CSA	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.5 cm
Package 1 Width	12.0 cm
Package 1 Length	18.0 cm

Package 1 Weight	36.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	9.5 cm
Package 2 Width	12.0 cm
Package 2 Length	18.0 cm
Package 2 Weight	217.0 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	96
Package 3 Height	30.0 cm
Package 3 Width	40.0 cm
Package 3 Length	60.0 cm
Package 3 Weight	5.002 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations