





APC NetShelter 12U Wallmount Rack Enclosure Cabinet Single Hinged Server Depth

AR112SH6

Overview

Presentation

Ideal for retail, healthcare, and educational facilities, this wall mount rack offers an efficient solution for deploying server and networking equipment for edge computing applications. This rack enclosure is wall mountable, ideal for areas with limited floor space, and is designed specifically for servers and network switches and patch panels. The cabinet's door is reversible and is compatible with APC's Netbotx security upgrade to provide remote access, video surveillance, and environmental monitoring (sold separately). Optional 120V fan tray can be top or bottom mounted (sold separately) Both the top and bottom feature knockouts of 1/2U mounting space for accessories. And several APC Smart-UPS models low-profile provide easy UPS integration and mounting 12U Wall mount cabinet, mounting depth range of 2.87 to 20.8 inches, 200lb weight capacity, 19"" rack width, ships fully assembled, ventilated with accessory integration options, 5 year APC warranty.

Lead Time

Usually in Stock

Main

Product Or Component Type	Rack enclosure
Number Of Rack Unit	12U

Physical

Height	62 cm
Width	60 cm
Depth	60 cm
Net Weight	19.19 kg
Colour	Black
Mounting Support	Wall
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	52.83 cm
Minimum Mounting Depth	7.29 cm
Rack Width	19"
Permanent Permissible Load	90.72 kg static

Conformance

Packing Units

Unit Type Of Package 1 PCE

Number Of Units In Package 1	1
Package 1 Height	70 cm
Package 1 Width	68.5 cm
Package 1 Length	68.5 cm
Package 1 Weight	23.18 kg

Contractual warranty

Warranty 5 year repair or replace



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >









Energy Efficient Take-back Transparency RoHS/REACh

Resource performance

Energy Efficient Product



Take-Back Program Available

Well-being performance

Reach Free Of Svhc



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

EU RoHS Declaration

China Rohs Regulation

China RohS declaration

Pro-active China RoHS declaration (out of China RoHS legal scope)

Environmental Disclosure

Product Environmental Profile