


# Product datasheet

Specifications



NFC cartridge fuses, TeSys GS, cylindrical, 22mm x 58mm, fuse type gG, 690VAC, 20A, without striker

DF2FN20

 **Discontinued on:** 9 Feb 2023

 **Discontinued**

## Main

Range Of Product	TeSys fuse-disconnector
Product Or Component Type	Cartridge fuse
Device Short Name	DF2
[Ue] Rated Operational Voltage	690 V AC
[In] Rated Current	20 A 690 V
Fuse Size	22 x 58 mm
Fuse Type	NFC
Quantity Per Set	Set of 10

## Complementary

Fuse Curve	GG
Net Weight	0.045 kg

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.200 cm
Package 1 Width	11.500 cm
Package 1 Length	12.000 cm
Package 1 Weight	50.900 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	2.200 cm
Package 2 Width	11.500 cm
Package 2 Length	12.000 cm
Package 2 Weight	516.000 g
Unit Type Of Package 3	S01
Number Of Units In Package 3	50
Package 3 Height	15.000 cm
Package 3 Width	15.000 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 3 Length	40.000 cm
Package 3 Weight	2.765 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Pvc Free	
Reach Regulation	<a href="#">REACH Declaration</a>	
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>	
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	