

# Product datasheet

Specifications



## Ultimate Slimline - surface surface mounted box - 1 gang

GU9135

### Main

|                           |                     |
|---------------------------|---------------------|
| Range Of Product          | Ultimate            |
| Aesthetic Name            | Slimline            |
| Product Or Component Type | Surface mounted box |
| Colour Tint               | White               |
| Quantity Per Set          | Set of 10           |

### Complementary

|                 |                  |
|-----------------|------------------|
| Device Mounting | Surface          |
| Number Of Gangs | 1 gang           |
| Cable Entry     | Knock-out        |
| Fixing Mode     | By screws        |
| Material        | Urea (carbamide) |
| Depth           | 38.5 mm          |
| Width           | 87.8 mm          |
| Height          | 87.8 mm          |
| Net Weight      | 0.093 kg         |

### Environment

|           |               |
|-----------|---------------|
| Standards | BS EN 60670-1 |
|-----------|---------------|

### Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type Of Package 1       | PCE     |
| Number Of Units In Package 1 | 1       |
| Package 1 Height             | 3.8 cm  |
| Package 1 Width              | 8.8 cm  |
| Package 1 Length             | 8.8 cm  |
| Package 1 Weight             | 92 g    |
| Unit Type Of Package 2       | BB1     |
| Number Of Units In Package 2 | 10      |
| Package 2 Height             | 9.5 cm  |
| Package 2 Width              | 18.8 cm |
| Package 2 Length             | 23.5 cm |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                              |          |
|------------------------------|----------|
| Package 2 Weight             | 1.042 kg |
| Unit Type Of Package 3       | CAR      |
| Number Of Units In Package 3 | 200      |
| Package 3 Height             | 39 cm    |
| Package 3 Width              | 48 cm    |
| Package 3 Length             | 50.5 cm  |
| Package 3 Weight             | 21.31 kg |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

# Sustainability


**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

|  |  |
|--|--|
|  Rohs Exemption Information | Yes  |
| <hr/>  |  |
| Reach Regulation   | <a href="#">REACH Declaration</a>                          |
| <hr/>  |  |
| Eu Rohs Directive  | Pro-active compliance (Product out of EU RoHS legal scope) |
| <hr/>  |  |
| China Rohs Regulation  | <a href="#">China RoHS declaration</a>                     |
| <hr/>  |  |
| Circularity Profile  | No need of specific recycling operations                   |
| <hr/>  |  |