
Product datasheet

Specifications





Flange feed unit, Canalis KSA400, aluminium, 400A, right or left mounting, without line protection, 3L+N+PE, RAL9001

KSA400AE4

Main

Range Of Product	Canalis
Product Name	KS
Device Short Name	KSA
Product Compatibility	Canalis KSA busbar trunking 400 A
Offer Type	Advanced Rising main
Product Or Component Type	Flange feed unit
Conductors Material	Aluminium
[le] Rated Operational Current	400 A
[Ue] Rated Operational Voltage	230690 V
Number Of Circuits	1
Busbar Trunking Polarity	3L + N + PE
Protection Type	Without protection
Control Type	Without
Colour	White (RAL 9001)

Complementary

Provided Equipment	End cover
Mounting Location	Right Left
Mounting Mode	By screws
Mounting Support	Busbar
Body Material	Metal
Connections - Terminals	Bar
Width	279.5 mm
Depth	81 mm
Height	334 mm
Net Weight	2.1 kg
Standards	IEC 61439-1 IEC 61439-6

Environment

Ip Degree Of Protection IP55 conforming to IEC 60529

Ik Degree Of Protection IK08 conforming to IEC 62262

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.0 cm
Package 1 Width	22.0 cm
Package 1 Length	39.0 cm
Package 1 Weight	2.74 kg
Unit Type Of Package 2	P06
Number Of Units In Package 2	30
Package 2 Height	88 cm
Package 2 Width	60 cm
Package 2 Length	80 cm
Package 2 Weight	90 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
⊘	Halogen Free Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations