# **Product datasheet**

Specifications





Pragma - single or three phase control block -surface- 18 modules - without door

PRA50818

! Discontinued on: 20 Nov 2023

! Discontinued

#### Main

Range Of Product	Pragma
Product Or Component Type	Control block
Accessory / Separate Part Category	Installation accessory
Network Connection	Single phase Three phase
Installed Device	DB 90

### Complementary

Range Compatibility	Pragma
Enclosure Mounting	Surface
Number Of Horizontal Rows	2
9 Mm Pitches	36
Number Of 18 Mm Modules Per Row	18
Total Number Of 18 Mm Modules	18
Provided Equipment	DIN rail 2 36
Enclosure Material	Technoplastic
Width	426 mm
Height	450 mm
Depth	123 mm
Colour	Titanium white

#### **Environment**

<b>Product Certifications</b>	EDF
Electrical Insulation Class	Class II
Fire Resistance	Front face: 750 °C
Ip Degree Of Protection	IP30
Ik Degree Of Protection	IK08
Ambient Air Temperature For Operation	-2560 °C

#### **Packing Units**

Unit Type Of Package 1 PCE

Number Of Units In Package 1	1
Package 1 Height	13.500 cm
Package 1 Width	51.000 cm
Package 1 Length	53.000 cm
Package 1 Weight	3.762 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	24
Package 2 Height	120.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	141.600 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations  Circularity Profile