Product datasheet





modem interface - analog PSTN for communication interface SR2COM01

SR2MOD01

! Discontinued on: 12 Feb 2021

(!) Discontinued

Main

| Range Of Product | Modicon M251 Modicon M221 |
|---------------------------|------------------------------|
| | Zelio Logic |
| | Modicon M241 |
| Product Or Component Type | Analogue PSTN modem |
| Type Of Modem | SIXNET VT-MODEM-5-WW |
| Data Backed Up | Flash memory |

| Complementary | |
|---------------------------|--|
| Kit Composition | Analogue PSTN modem |
| | 1 telephone cable |
| Function Available | Transfer program |
| | Update firmware monitoring |
| | Send alarm/receive instruction |
| | Send alarm to e-mail address |
| Number Of Messages | 28 |
| Electrical Data Recording | Telephone/e-mail |
| | Discrete and digital value |
| | Date and time |
| [Us] Rated Supply Voltage | 1224 V DC |
| Supply Voltage Limits | 1030 V |
| Maximum Supply Current | 140 mA at 12 V |
| | 70 mA at 24 V |
| | 9600 mA |
| Power Dissipation In W | 1.7 W |
| Electrical Connection | 1 cable Com-M specific to Zelio RS232 serial, specific Zelio communication protocol |
| | for link with the modem, AT commands |
| | 1 cable Com-Z specific to Zelio, specific Zelio communication protocol for Zelio Logic |
| | smart relays SR.B and SR2 E Version (>= V3.1) |
| | Telephone cable |
| Cable Length | 2 m |
| Insulation | 1780 V optocoupler, connector type: Com-Z specific to Zelio |
| | By the cable SR2 CBL07, connector type: Com-M specific to Zelio |
| Connections - Terminals | Screw terminals, 1 x 0.251 x 2.5 mm² (AWG 24AWG 14) flexible with cable end |
| | Screw terminals, 2 x 0.252 x 0.75 mm² (AWG 24AWG 18) flexible with cable end |
| | Screw terminals, 1 x 0.251 x 2.5 mm² (AWG 24AWG 14) semi-solid |
| | Screw terminals, 1 x 0.251 x 2.5 mm² (AWG 24AWG 14) solid |
| | Screw terminals, 2 x 0.252 x 1.5 mm ² (AWG 23AWG 16) solid |
| Tightening Torque | 0.5 N.m |
| Net Weight | 0.265 kg |
| | |

Life Is On Schneider 26 Apr 2024

Environment

| Product Certifications | FCC part 15 standard C-Tick ACA TS CTR21 GOST UL AS/NZS CSA |
|---------------------------------------|---|
| Standards | EN/IEC 60068-2-27 Ea EN/IEC 61000-4-5 EN/IEC 60068-2-6 Fc |
| Electromagnetic Compatibility | Conducted and radiated emissions class B group 1 conforming to EN 55022-11 |
| Ip Degree Of Protection | IP20 (terminal block) conforming to IEC 60529 IP40 (front panel) conforming to IEC 60529 |
| Environmental Characteristic | EMC directive conforming to EN/IEC 61000-6-2 EMC directive conforming to EN/IEC 61000-6-3 EMC directive conforming to EN/IEC 61000-6-4 EMC directive conforming to EN/IEC 61131-2 zone B Low voltage directive conforming to EN/IEC 61131-2 |
| Pollution Degree | 2 conforming to EN/IEC 61131-2 |
| Ambient Air Temperature For Operation | -3070 °C |
| Ambient Air Temperature For Storage | -4085 °C |
| Operating Altitude | 2000 m |
| Maximum Altitude Transport | 3048 m |
| Relative Humidity | 595 % without condensation |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|---------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 6 cm |
| Package 1 Width | 14.5 cm |
| Package 1 Length | 15.3 cm |
| Package 1 Weight | 262 g |

Contractual warranty

| Warranty 18 months | |
|--------------------|--|
|--------------------|--|



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| ⊘ | Toxic Heavy Metal Free | |
|----------|----------------------------|-----|
| Ø | Mercury Free | |
| ⊘ | Rohs Exemption Information | Yes |
| ⊘ | Pvc Free | |


Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End of Life Information |

Dimensions Drawings

Analogue PSTN Modem

Rail Mounting



Screw Fixing

