



rotating mirror beacon XVR - Ø 165 - blue - 25 W - 24 V AC DC

XVR1B06

! Discontinued on: 29 Jan 2021

(!) Discontinued

Main

Range Of Product	Harmony XVR Application	
Product Or Component Type	Rotating mirror beacon	
Component Name	XVR	
Mounting Diameter	165 mm	
Light Source	Bulb included, blue	
Bulb Type	Incandescent with BA 15d base	
Power Dissipation In W	25 W	
[Us] Rated Supply Voltage	24 V AC/DC	

Complementary

Material	Glass reinforced polyamide 6: base unit Polycarbonate: domed lens unit	
Clamping Connection Capacity	<= 1 x 1.5 mm²	
Cable Entry	1 tapped entry for cable gland (included) for M20	
[Ui] Rated Insulation Voltage	250 V conforming to EN/IEC 60947-1	
Current Consumption	< 1050 mA	
[Uimp] Rated Impulse Withstand Voltage	4 kV conforming to EN/IEC 60947-1	
Service Life In Hours	2000 h	
Operating Position	Horizontal	
Flashing Frequency	3 Hz	
Cad Overall Width	165 mm	
Cad Overall Height	202 mm	
Cad Overall Depth	165 mm	
Net Weight	1.165 kg	

Environment

Standards	EN/IEC 60947-5-1 CSA C22.2 No 14 EN/IEC 60947-1 UL 508
Protective Treatment	TC
Ambient Air Temperature For	-4070 °C

Ambient Air Temperature For Operation	-2050 °C
Electrical Shock Protection Class	Class I conforming to EN/IEC 61140
Ip Degree Of Protection	IP65 conforming to IEC 60529
Nema Degree Of Protection	NEMA 4X conforming to UL 508 (indoor) NEMA 4X conforming to CSA C22 (indoor)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Toxic Heavy Metal Free	
	Mercury Free	
②	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information