# **Product datasheet**





# FRONT PLATE VIGI NSX630 **VERTICAL FIXED TOGGLE W300** 10M

03299

! Discontinued on: 12 May 2023



### Main

Range	Prisma
Range Of Product	Prisma G Prisma P
Product Or Component Type	Front plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma G duct Prisma Prisma P cubicle
Type Of Front Plate	Cut-out
Installed Device	ComPact: fixed NSX400 with earth leakage protection - control: toggle - vertical installation ComPact: plug-in NSX400 with earth leakage protection - control: toggle - vertical installation ComPact: fixed NSX630 with earth leakage protection - control: toggle - vertical installation ComPact: plug-in NSX630 with earth leakage protection - control: toggle - vertical installation
Poles Description	1 x 4P: mounting plate support: NSX400 vertical installation 1 x 3P: mounting plate support: NSX400 vertical installation 1 x 3P: mounting plate support: NSX630 vertical installation 1 x 4P: mounting plate support: NSX630 vertical installation
Operating Position	Vertical

### Complementary

Enclosure/Cubicle Description	Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm Cubicle duct - width 400 mm depth 400 mm	
Connection Position	Direct connection Front connection	
Number Of Vertical Modules [50 Mm]	ertical Modules [50 g	
Standards	IEC 61439-1 IEC 61439-2	
Product Certifications	ASEFA	
Material	Steel	
Surface Finish	Matt Smooth	
Protective Treatment	Treatment Electrophoresis treatment and hot-polymerised polyester epoxy powder	
Colour	White (RAL 9001)	
Height	500 mm	

Life Is On Schneider 25 Apr 2024

Width	250 mm
Net Weight	1 kg
Quantity Per Set	Set of 1
Functional Unit	300 mm Prisma G floor-standing duct ComPact NSX400 with fixed toggle vertical 4P
	1 direct 300 mm Prisma G wall-mounted duct ComPact NSX400 with fixed toggle vertical 4P
	1 direct
	400 mm 400 mm Prisma P cubicle ComPact NSX400 with fixed toggle vertical 3P 1
	front connection 14
	400 mm 400 mm Prisma P cubicle ComPact NSX400 with fixed toggle vertical 4P 1
	front connection 14
	400 mm 400 mm Prisma P cubicle ComPact NSX400 with plug-in toggle vertical 3P 1
	front connection 14
	400 mm 400 mm Prisma P cubicle ComPact NSX400 with plug-in toggle vertical 4P 1
	front connection 14
	400 mm 400 mm Prisma P cubicle ComPact NSX630 with fixed toggle vertical 3P 1 front connection 14
	400 mm 400 mm Prisma P cubicle ComPact NSX630 with fixed toggle vertical 4P 1
	front connection 14
	400 mm 400 mm Prisma P cubicle ComPact NSX630 with plug-in toggle vertical 3P 1
	front connection 14
	400 mm 400 mm Prisma P cubicle ComPact NSX630 with plug-in toggle vertical 4P 1
	front connection 14
	300 mm Prisma G floor-standing duct ComPact NSX400 with fixed toggle vertical 3P
	1 direct with long terminal shield 14
	300 mm Prisma G wall-mounted duct ComPact NSX400 with fixed toggle vertical 3P
	1 direct with long terminal shield 14
	300 mm Prisma G floor-standing duct ComPact NSX400 with fixed toggle vertical 4P
	1 direct with long terminal shield 14
	300 mm Prisma G wall-mounted duct ComPact NSX400 with fixed toggle vertical 4P
	1 direct with long terminal shield 14
	300 mm Prisma G floor-standing duct ComPact NSX630 with fixed toggle vertical 3P 1 direct with long terminal shield 14
	300 mm Prisma G wall-mounted duct ComPact NSX630 with fixed toggle vertical 3P
	1 direct with long terminal shield 14
	300 mm Prisma G floor-standing duct ComPact NSX630 with fixed toggle vertical 4P
	1 direct with long terminal shield 14
	300 mm Prisma G wall-mounted duct ComPact NSX630 with fixed toggle vertical 4P
	1 direct with long terminal shield 14

## **Packing Units**

r doming office	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.700 cm
Package 1 Width	26.000 cm
Package 1 Length	51.000 cm
Package 1 Weight	992.000 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	16.500 cm
Package 2 Width	27.900 cm
Package 2 Length	52.800 cm
Package 2 Weight	10.188 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	270
Package 3 Height	93.500 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm

Package 3 Weight

287.076 kg



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>⊘</b>	Reach Free Of Svhc
<b>⊘</b>	Toxic Heavy Metal Free
<b>⊘</b>	Mercury Free
<b>⊘</b>	Rohs Exemption Information Yes
<b>⊘</b>	Halogen Free Plastic Parts Product

### **Certifications & Standards**

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile