


# Product datasheet

Specifications



## MOUNTING PLATE FOR EZC FIXED -1P/3P/4P 100A VERTICAL IN WIDTH 650

03502

⚠ Discontinued on: 12 May 2023

⚠ Discontinued

### Main

Range	Prisma
Range Of Product	Prisma P
Product Or Component Type	Mounting plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma P cubicle
Installation Description	Cubicle - width 650 mm depth 400 mm
Installed Device	EasyPact: fixed EZC100 without earth leakage protection - control: toggle - vertical installation
Poles Description	15 x 1P: fixed EZC100 vertical installation 5 x 3P: fixed EZC100 vertical installation 3 x 4P: fixed EZC100 vertical installation
Number Of Vertical Modules [50 Mm]	5 module(s): EZC100 without earth leakage protection , direct in 650 mm Widecubicle
Standards	IEC 61439-2
Product Certifications	ASEFA

### Complementary

Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface Finish	Smooth Matt
Colour	White (RAL 9001)
Width	575 mm
Height	147 mm
Net Weight	2.2 kg
Functional Unit	650 mm 400 mm Prisma P cubicle EasyPact EZC100 without fixed toggle vertical 1P 15 direct 5 62.5 mm 650 mm 400 mm Prisma P cubicle EasyPact EZC100 without fixed toggle vertical 3P 5 direct 5 62.5 mm 650 mm 400 mm Prisma P cubicle EasyPact EZC100 without fixed toggle vertical 4P 3 direct 5 62.5 mm

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.000 cm

Package 1 Width	15.000 cm
Package 1 Length	59.000 cm
Package 1 Weight	2.200 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	6
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	14.060 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	24
Package 3 Height	60.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	63.120 kg

## Contractual warranty

Warranty	12 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

## Well-being performance

Mercury Free

Rohs Exemption Information [Yes](#)

Halogen Free Plastic Parts Product

## Certifications & Standards

### Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

### China Rohs Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

### Environmental Disclosure

[Product Environmental Profile](#)

### Circularity Profile

[End of Life Information](#)