Product datasheet

Specifications





FR.PL.HZ.NS630 C/OVER MOT.

03656

Discontinued on: 12 May 2023

! Discontinued

Main

Range	Prisma
Range Of Product	Prisma P
Product Or Component Type	Front plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma P cubicle
Type Of Front Plate	Cut-out
Installed Device	Source changeover: fixed NSX400630 source changeover without earth leakage protection - control: remote control - horizontal installation
Poles Description	2 x 3P: mounting plate support: NSX400630 source changeover horizontal installation 2 x 4P: mounting plate support: NSX400630 source changeover horizontal installation
Operating Position	Horizontal

Complementary

Enclosure/Cubicle Description	Cubicle - width 650 mm depth 400 mm
Connection Position	Direct connection
Number Of Vertical Modules [50 Mm]	10
Standards	IEC 61439-2 IEC 61439-1
Product Certifications	ASEFA
Material	Steel
Surface Finish	Matt Smooth
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	500 mm
Width	500 mm
Net Weight	1.72 kg
Quantity Per Set	Set of 1
Functional Unit	650 mm 400 mm Prisma P cubicle source changeover NSX400630 source changeover without fixed remote control horizontal 3P 2 direct 10

650 mm 400 mm Prisma P cubicle source changeover NSX400...630 source changeover without fixed remote control horizontal 4P 2 direct 10

25 Apr 2024 Life Is On Schneider

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.000 cm
Package 1 Width	51.000 cm
Package 1 Length	51.000 cm
Package 1 Weight	1.720 kg
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	11.000 cm
Package 2 Width	53.000 cm
Package 2 Length	53.000 cm
Package 2 Weight	10.320 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	72
Package 3 Height	75.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	135.840 kg

Contractual warranty

Warranty 12 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
⊘	Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	
China Rons Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	
Environmental Disclosure	Product Environmental Profile
Circularity Profile	Find of Utility Information
On outainty i forme	End of Life Information