


Product datasheet

Specifications



Front Plate Vert. Fixed MTZ1/NT 3P W400 Prisma P

03698

! Discontinued on: 15 Jun 2023

! Discontinued

Main

Range	Prisma
Range Of Product	Prisma P
Product Or Component Type	Front plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma P cubicle
Type Of Front Plate	Cut-out
Installed Device	Masterpact: fixed NT06...10 - control: toggle - vertical installation Masterpact: fixed NT12 - control: toggle - vertical installation Masterpact: fixed NT16 - control: toggle - vertical installation
Poles Description	1 x 3P: mounting plate support: NT06...10 vertical installation 1 x 3P: mounting plate support: NT12 vertical installation 1 x 3P: mounting plate support: NT16 vertical installation
Operating Position	Horizontal

Complementary

Enclosure/Cubicle Description	Cubicle duct - width 400 mm depth 400 mm
Connection Position	Front connection
Number Of Vertical Modules [50 Mm]	11
Standards	IEC 61439-1 IEC 61439-2
Product Certifications	ASEFA
Material	Steel
Surface Finish	Smooth Matt
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	550 mm
Width	321 mm
Net Weight	1.88 kg
Quantity Per Set	Set of 1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Functional Unit	400 mm 400 mm Prisma P cubicle Masterpact NT06...10 fixed toggle vertical 3P 1 front connection 36 400 mm 400 mm Prisma P cubicle Masterpact NT12 fixed toggle vertical 3P 1 front connection 36 400 mm 400 mm Prisma P cubicle Masterpact NT16 fixed toggle vertical 3P 1 front connection 36
-----------------	--

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	35.0 cm
Package 1 Length	55.5 cm
Package 1 Weight	1.88 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	7
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	13.16 kg

Contractual warranty

Warranty	12 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information