
Product datasheet





FRONT PLATE WITH 6 CUT-OUT 72x72METERING DEV/P-BUTTON WIDTH 600/650 3M

03910

! Discontinued on: 12 May 2023

! Discontinued

Main

Range	Prisma	
Range Of Product	Prisma G Prisma P	
Product Or Component Type	Front plate	
Accessory / Separate Part Category	Installation accessory	
Range Compatibility	Prisma Prisma G enclosure Prisma Prisma P cubicle	
Type Of Front Plate	Cut-out	
Type Of Front Plate	Cut-out	
Installed Device	Vigirex: RH10 Vigirex: RH21 Vigirex: RH99 Human-switchboard interface: 72 x 72 mm device Human-switchboard interface: HSI	

Human-switchboard interface: HSI

Complementary

Enclosure/Cubicle Description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Cubicle - width 650 mm depth 400 mm
Number Of Vertical Modules [50 Mm]	3
Standards	IEC 61439-1 IEC 61439-2
Product Certifications	ASEFA
Material	Steel
Surface Finish	Smooth Matt
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	150 mm
Width	500 mm
Net Weight	0.48 kg
Quantity Per Set	Set of 1

Functional Unit

650 mm 400 mm Prisma P cubicle Vigirex 6 3
600 mm Prisma G floor-standing enclosure human-switchboard interface 72 x 72 mm
device 6 3
600 mm Prisma G wall-mounted enclosure human-switchboard interface 72 x 72 mm
device 6 3
650 mm 400 mm Prisma P cubicle human-switchboard interface 72 x 72 mm device
6 3
600 mm Prisma G floor-standing enclosure human-switchboard interface HSI 6 3
600 mm Prisma G wall-mounted enclosure human-switchboard interface HSI 6 3
650 mm 400 mm Prisma P cubicle human-switchboard interface HSI 6 3
600 mm Prisma G floor-standing enclosure Vigirex 6 3
600 mm Prisma G wall-mounted enclosure Vigirex 6 3

Packing Units

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	16.0 cm
Package 1 Length	52.0 cm
Package 1 Weight	480.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	17.5 cm
Package 2 Width	17.0 cm
Package 2 Length	53.0 cm
Package 2 Weight	5.5 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	90
Package 3 Height	32.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	61.5 kg

Contractual warranty

Warranty 12 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
Ø	Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile