
Product datasheet





FRONT PLATE WITH 1 CUT-OUT 96x96METERING DEV/P-BUTTON WIDTH 600/650 3M

03913

! Discontinued on: 12 May 2023

! Discontinued

Main

Range	Prisma
Range Of Product	Prisma G Prisma P
Product Or Component Type	Front plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma G enclosure Prisma Prisma P cubicle
Type Of Front Plate	Cut-out
Type Of Front Plate	Cut-out
Installed Device	Human-switchboard interface: 96 x 96 mm device PowerLogic: PM5500 Human-switchboard interface: HSI PowerLogic: PM400800 PowerLogic: PM5100 PowerLogic: PM5300 PowerLogic: PM5563RD Enerlin'X: FDM121

Complementary

Enclosure/Cubicle Description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Cubicle - width 650 mm depth 400 mm	
Number Of Vertical Modules [50 Mm]	3	
Standards	IEC 61439-2 IEC 61439-1	
Product Certifications	ASEFA	
Material	Steel	
Surface Finish	Smooth Matt	
Protective Treatment	eatment Electrophoresis treatment and hot-polymerised polyester epoxy powder	
Colour	White (RAL 9001)	
Height	150 mm	
Width	500 mm	
Net Weight	0.62 kg	
Quantity Per Set	Set of 1	

Functional Unit	600 mm Prisma G floor-standing enclosure human-switchboard interface 96 x 96 mm device 1.3
	600 mm Prisma G wall-mounted enclosure human-switchboard interface 96 x 96 mm device 1 3
	650 mm 400 mm Prisma P cubicle human-switchboard interface 96 x 96 mm device 1 3
	600 mm Prisma G floor-standing enclosure human-switchboard interface HSI 1 3
	600 mm Prisma G wall-mounted enclosure human-switchboard interface HSI 1 3
	650 mm 400 mm Prisma P cubicle human-switchboard interface HSI 1 3
	600 mm Prisma G floor-standing enclosure PowerLogic 1 3
	600 mm Prisma G wall-mounted enclosure PowerLogic 1 3
	650 mm 400 mm Prisma P cubicle PowerLogic 1 3
	600 mm Prisma G floor-standing enclosure Enerlin'X FDM121 1 3
	600 mm Prisma G wall-mounted enclosure Enerlin'X FDM121 1 3
	650 mm 400 mm Prisma P cubicle Enerlin'X FDM121 1 3

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.600 cm
Package 1 Width	16.000 cm
Package 1 Length	52.000 cm
Package 1 Weight	600.000 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	17.000 cm
Package 2 Width	17.600 cm
Package 2 Length	52.500 cm
Package 2 Weight	6.327 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	90
Package 3 Height	32.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	60.960 kg

Contractual warranty

Warranty	12 months	
----------	-----------	--



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
⊘	Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile