



MOUNTING PLATE FOR 4 NSXm VIGI TOGGLE -3P/4P VERTICAL WIDTH 650

03406

! Discontinued on: 12 May 2023

(!) Discontinued

Main

Range	Prisma
Range Of Product	Prisma P
Product Or Component Type	Mounting plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma P cubicle ComPact ComPact NSXm circuit breaker
Installation Description	Cubicle - width 650 mm depth 400 mm
Mounting Plate Description	Dedicated
Installed Device	ComPact: fixed NSXm with earth leakage protection - control: toggle - vertical installation
Poles Description	4 x 3P or 4P: fixed NSXm vertical installation
Number Of Vertical Modules [50 Mm]	8 module(s): NSXm with earth leakage protection , direct
Standards	IEC 61439-2
Product Certifications	ASFFA

Complementary

Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface Finish	Smooth Matt
Colour	White (RAL 9001)
Width	575 mm
Height	150 mm
Functional Unit	650 mm 400 mm Prisma P cubicle ComPact NSXm with fixed toggle vertical 3P or 4P 4 direct 8 162.5 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.800 cm
Package 1 Width	15.300 cm
Package 1 Length	57.800 cm
Package 1 Weight	2.524 kg

Unit Type Of Package 2	S04
Number Of Units In Package 2	6
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	15.899 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	72
Package 3 Height	103.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	202.788 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
⊘	Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	
China Rons Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	
Environmental Disclosure	Product Environmental Profile
Circularity Profile	Find of Utility Information
On outainty i forme	End of Life Information