
# **Product datasheet**

Specifications





### FR.PL.INS1600 3P

03713

Discontinued on: 12 May 2023



### Main

Range	Prisma
Range Of Product	Prisma P
Product Or Component Type	Front plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma P cubicle
Type Of Front Plate	Cut-out
Installed Device	ComPact: fixed INS630b1600 - control: direct front rotary handle - vertical installation ComPact: fixed INV630b1600 - control: direct front rotary handle - vertical installation
Poles Description	1 x 3P: mounting plate support: INS630b1600 vertical installation 1 x 3P: mounting plate support: INV630b1600 vertical installation
Operating Position	Vertical

## Complementary

Enclosure/Cubicle Description	Cubicle - width 650 mm depth 400 mm
Connection Position	Rear connection
	Front connection
Number Of Vertical Modules [50 Mm]	6
Standards	IEC 61439-1
	IEC 61439-2
Product Certifications	ASEFA
Material	Steel
Surface Finish	Smooth
	Matt
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	300 mm
Width	500 mm
Net Weight	1.04 kg
Quantity Per Set	Set of 1
Functional Unit	650 mm 400 mm Prisma P cubicle ComPact INS630b1600 fixed direct front rotary handle vertical 3P 1 front connection on adaptor 14 650 mm 400 mm Prisma P cubicle ComPact INV630b1600 fixed direct front rotary
	handle vertical 3P 1 front connection on adaptor 14

19 Apr 2024 Life Is On Schneider

## **Packing Units**

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.200 cm
Package 1 Width	29.900 cm
Package 1 Length	50.300 cm
Package 1 Weight	1.050 kg
Unit Type Of Package 2	CAR
Number Of Units In Package 2	16
Package 2 Height	39.000 cm
Package 2 Width	42.000 cm
Package 2 Length	52.000 cm
Package 2 Weight	17.150 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	128
Package 3 Height	90.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	138.880 kg

### **Contractual warranty**

Warranty 12 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>Ø</b>	Toxic Heavy Metal Free	
<b>9</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information