
Product datasheet

Specifications

Sreen Premium[™]



FRONT PLATE 1CUT-OUT144x144 +4CUT-OUT72x72 METERING DEV/P-BUTTON WIDTH600/650 4M

03912

① Discontinued

() Discontinued on: 12 May 2023

Main

Range	Prisma
Range Of Product	Prisma G Prisma P
Product Or Component Type	Front plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma G enclosure Prisma Prisma P cubicle
Type Of Front Plate	Cut-out
Type Of Front Plate	Cut-out
Installed Device	Human-switchboard interface: HSI Human-switchboard interface: 144 x 144 mm device and 72 x 72 mm device

Complementary

Enclosure/Cubicle Description	Floor-standing enclosure - width 600 mm
	Wall-mounted enclosure - width 600 mm
	Cubicle - width 650 mm depth 400 mm
Number Of Vertical Modules [50 Mm]	4
Standards	IEC 61439-2
	IEC 61439-1
Product Certifications	ASEFA
Material	Steel
Surface Finish	Smooth
	Matt
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	200 mm
Width	500 mm
Net Weight	0.62 kg
Quantity Per Set	Set of 1

600 mm Prisma G floor-standing enclosure human-switchboard interface 144 x 144 mm device and 72 x 72 mm device 5 4 600 mm Prisma G wall-mounted enclosure human-switchboard interface 144 x 144 mm device and 72 x 72 mm device 5 4 650 mm 400 mm Prisma P cubicle human-switchboard interface 144 x 144 mm device and 72 x 72 mm device 5 4 600 mm Prisma G floor-standing enclosure human-switchboard interface HSI 5 4 600 mm Prisma G wall-mounted enclosure human-switchboard interface HSI 5 4 650 mm 400 mm Prisma P cubicle human-switchboard interface HSI 5 4

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.000 cm
Package 1 Width	21.000 cm
Package 1 Length	51.000 cm
Package 1 Weight	620.000 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	16.000 cm
Package 2 Width	22.000 cm
Package 2 Length	53.000 cm
Package 2 Weight	7.700 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	20
Package 3 Height	30.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	15.400 kg

Contractual warranty

Warranty

12 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Halogen Free Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations