



Connection Horiz. LGYE MTZ2/ NW 1600A 4P Prisma P

Discontinued on: 15 Jun 2023

! Discontinued

Main

Range	Prisma	
Range Of Product	Prisma P	
Product Or Component Type	Connection	
Product Name	Prisma Prisma P enclosure Masterpact MasterPact NW circuit breaker	
Accessory / Separate Part Category	Current distribution accessory	
Standards	IEC 61439-2 IEC 61439-1	
Product Certifications	ASEFA	

Complementary

Cubicle-Device Connection	connection transfer assembly
Poles Description	4P
Installation Description	Cubicle - width 650 mm
Cubicle Depth	600 mm: front 600 + 400 mm: rear
Installed Device	Masterpact: drawout NW0816 - control: toggle vertical installation Masterpact: fixed NW0816 - control: toggle vertical installation
[le] Rated Operational Current	1600 A
[In] Rated Current	1600 A
Length	580 mm
Quantity Per Set	Set of 1

Functional Unit	650 mm 600 mm Prisma P cubicle Masterpact NW0816 drawout toggle vertical 4P
	1 front connection on adaptor 36
	650 mm 600 mm Prisma P cubicle Masterpact NW0816 drawout toggle vertical 4P
	1 front connection on Canalis 27
	650 mm 1000 mm Prisma P cubicle Masterpact NW0816 drawout toggle vertical
	4P 1 rear connection on adaptor 15
	650 mm 600 mm Prisma P cubicle Masterpact NW0816 drawout toggle vertical 4P
	1 front connection on adaptor 19
	650 mm 1000 mm Prisma P cubicle Masterpact NW0816 drawout toggle vertical
	4P 1 rear connection on Canalis 17
	650 mm 600 mm Prisma P cubicle Masterpact NW0816 drawout toggle vertical 4P
	1 front connection on busbar 36
	650 mm 600 mm Prisma P cubicle Masterpact NW0816 fixed toggle vertical 4P 1
	front connection on adaptor 18
	650 mm 1000 mm Prisma P cubicle Masterpact NW0816 fixed toggle vertical 4P 1 rear connection on adaptor 14
	650 mm 600 mm Prisma P cubicle Masterpact NW0816 fixed toggle vertical 4P 1 front connection on Canalis 27
	650 mm 1000 mm Prisma P cubicle Masterpact NW0816 fixed toggle vertical 4P 1
	rear connection on Canalis 16
	650 mm 600 mm Prisma P cubicle Masterpact NW0816 fixed toggle vertical 4P 1
	front connection on busbar 36

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.1 cm
Package 1 Width	19.2 cm
Package 1 Length	61.5 cm
Package 1 Weight	8.77 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	24
Package 2 Height	40.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	222.48 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
Ø	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile