Product datasheet

Specifications





non - adjustable time delay relay for voltage release MN - 200/250 V AC/DC

33685

Main

| Device Short Name | MN delay unit |
|------------------------------|---------------------------------|
| Product Or Component Type | Time delay relay |
| Device Application | Control |
| Range Compatibility | Masterpact MasterPact NT |
| | Masterpact MasterPact NW |
| | ComPact ComPact NS630b1600 |
| | ComPact ComPact NS1600b3200 |
| | Masterpact MasterPact NW UL 489 |
| | Masterpact MasterPact NT UL 489 |
| | Masterpact MasterPact NW DC |
| Voltage Release Type | Undervoltage release |
| [Uc] Control Circuit Voltage | 200250 V AC 50/60 Hz |
| | 200250 V DC |

Complementary

| Impulse Duration | 200 ms |
|---------------------------------------|-------------------------------------------------------------------------|
| Time Delay Range | 0.25 s |
| Threshold Tripping Voltage | 0.350.7 Un open 0.85 Un close |
| Supply Holding Power | 4.5 VA |
| Supply Inrush Power | 200 VA |
| Mounting Mode | External mounting |
| Response Time | 0.25 s |
| Accessory / Separate Part Category | Spare part for Compact NS630b1600 Spare part for Compact NS1600b3200 |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|---------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 8.5 cm |
| Package 1 Width | 8.0 cm |
| Package 1 Length | 9.0 cm |
| Package 1 Weight | 147.0 g |
| Unit Type Of Package 2 | \$03 |
| Number Of Units In Package 2 | 36 |
| Package 2 Height | 30.0 cm |

| Package 2 Width | 30.0 cm |
|------------------|---------|
| Package 2 Length | 40.0 cm |
| Package 2 Weight | 5.73 kg |

Contractual warranty

Warranty

12 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|-------------------------------------------------------------------------------------------------------|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End of Life Information |