# **Product datasheet**

Specification





# Kaedra - versatile - 448 x 460 mm - 17 pre-cutouts

13197

## Main

Range	Mureva
Product Name	Mureva Enclosure
Product Or Component Type	Weatherproof enclosure
Enclosure Type	Versatile enclosure
Mounting Plate Description	Slotted

## Complementary

<b>Enclosure Mounting</b>	Surface
Electrical Insulation Class	Double insulation Class II
Type Of Front Cover	Opaque
Number Of Pre-Cutouts Pg Iso	17
Locking Options Description	Optional keylock
Enclosure Material	Self-extinguishing polymer
Width	448 mm
Height	460 mm
Depth	160 mm
Internal Depth	130 mm
Colour	Enclosure: light grey (RAL 7035)

## **Environment**

Standards	EN 50262 IEC 60695-2-1 IEC 61439-3 IEC 60670
Fire Resistance	650 °C conforming to IEC 60695-2-1
Ip Degree Of Protection	IP65 conforming to IEC 60529
Ik Degree Of Protection	IK09 conforming to EN 50102
Environmental Characteristics (Uv)	UV resistant: class 3 conforming to ISO 4582:2010 Ultraviolet degradation test conforming to ISO 4892-2:2013
Overvoltage Category	II
Ambient Air Temperature For Operation	-2560 °C

## **Packing Units**



Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	47.000 cm
Package 1 Width	46.800 cm
Package 1 Length	16.800 cm
Package 1 Weight	3.110 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	18
Package 2 Height	80.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	67.980 kg

## **Contractual warranty**

Warranty 18 months



Green Premium<sup>TM</sup> label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >








Lower Impact Materials Transparency RoHS/REACh

#### Resource performance



### Well-being performance



Rohs Exemption Information



Halogen Free Product

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations