Product datasheet

Specifications





Micrologic 5.0 - for Masterpact NW - fixed

65301

Main

Range	MasterPact
Range Of Product	MasterPact NW
Product Or Component Type	Control unit
Trip Unit Name	MicroLogic 5.0
Trip Unit Technology	Electronic
Range Compatibility	Masterpact NW0840 Masterpact NW40b63
Device Application	Distribution
Number Of Poles	4P 3P
Protected Poles Description	3t 3t + N/2 4t
Trip Unit Protection Functions	Selective protection
Protection Type	for short time short-circuit protection for overload protection (long time) for instantaneous short-circuit protection
Trip Unit Rating	800 A at 50 °C 1000 A at 50 °C 1250 A at 50 °C 1600 A at 50 °C 2000 A at 50 °C 2500 A at 50 °C 3200 A at 50 °C 4000 A at 50 °C 5000 A at 50 °C 6300 A at 50 °C
Network Type	AC
Network Frequency	50/60 Hz
Circuit Breaker Mounting Mode	Fixed

Complementary

Long-Time Pick-Up Adjustment Type Ir (Thermal Protection)	Adjustable 9 settings
[Ir] Long-Time Protection Pick-Up Adjustment Range	0.41 x ln
Long-Time Protection Delay Adjustment Type Tr	Adjustable 9 settings
[Tr] Long-Time Protection Delay Adjustment Range	0.716.6 s at 7.2 x lr 0.524 s at 6 x lr 12.5600 s at 1.5 x lr
Thermal Memory	20 mn

Short-Time Protection Pick-Up Adjustment Type Isd	Adjustable 9 settings	
[Isd] Short-Time Protection Pick- Up Adjustment Range	1.510 x lr	
Short-Time Protection Delay Adjustment Type Tsd	Adjustable	
[Tsd] Short-Time Protection Delay Adjustment Range	00.4 s l²t=off 0.10.4 s l²t=on	
Instantaneous Protection Pick-Up Adjustment Type Ii	Adjustable 9 settings	
[li] Instantaneous Protection Pick- Up Adjustment Range	215 x ln Off	
Earth-Leakage Protection	Without	
Zone Selective Interlocking Zsi	king Zsi Without	
Local Signalling	3 LEDs (red) for electrical fault 1 LED (red) for internal error	

Environment

Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-5085 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.8 cm
Package 1 Width	8.0 cm
Package 1 Length	21.5 cm
Package 1 Weight	365.0 g

Contractual warranty

Warranty 12 months

25 Apr 2024



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

	Mercury Free	
⊘	Rohs Exemption Information	Yes
⊘	Pvc Free	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information