



Mureva lights, Floodlight 20W 4000K, IP65 230V

IMT47208

Main

Range	Mureva
Range Of Product	Mureva lights
Product Or Component Type	Floodlight
Device Application	Ware-houses and parking garages Residential Media device support Public areas Secure lighting Stadiums and arenas

Complementary

Type Of Installation	Outdoor
Total System Power	20 W
Light Source	LED
[Ue] Rated Operational Voltage	230 V AC
Power Factor	0.7
Colour Rendering Index	R _a =80
Luminous Flux	2000 lm
Bulb Lifespan	50000 h
Colour Temperature	4000 K
Colour Tint	Black
Electrical Insulation Class	Class F
Beam Angle	110 °
Shape	Rectangular
Height	163.4 mm
Width	121.4 mm
Depth	26.0 mm
Net Weight	530 g

Environment

Environmental Characteristic	Weatherproof
Ip Degree Of Protection	IP65
Ik Degree Of Protection	IK05
Ambient Air Temperature For Operation	-3045 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	17.2 cm
Package 1 Width	17.2 cm
Package 1 Length	17.2 cm
Package 1 Weight	560 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	20
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	11.641 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	320
Package 3 Height	75 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	198.256 kg

Contractual warranty

Warranty 3 years



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >







Sustainable Packaging Transparency RoHS/REACh

Resource performance



Sustainable Packaging

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information