

Product datasheet

Specifications



Switch actuator REG-K/2x230/16 with manual mode, light grey

MTN647393

Main

Range Of Product	KNX
Product Or Component Type	Switch actuator
Operating Mode	Manual
Bus Type	KNX
Modular Device Additional Info	Connectable with different phases
Number Of Contacts	2

Complementary

Total Number Of 18 Mm Modules	2.5
Mounting Support	DIN rail
[Ue] Rated Operational Voltage	100...240 V
Network Frequency	50...60 Hz
[In] Rated Current	16 A
Load Type	Incandescent lamps: <= 3600 W, 230 V AC Halogen lamps: <= 2500 W, 230 V AC Incandescent lamps: <= 1600 W, 100 V AC Incandescent lamps: <= 3840 W, 240 V AC Halogen lamps: <= 1086 W, 100 V AC Halogen lamps: <= 2608 W, 240 V AC Parallel compensated fluorescent lamp: <= 1086 VA, 100 V AC Parallel compensated fluorescent lamp: <= 2500 VA, 230 V AC Parallel compensated fluorescent lamp: <= 2608 VA, 240 V AC Capacitive: , 16 A, 200 µF, 100...240 V AC

Environment

Ip Degree Of Protection	IP20
-------------------------	------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.100 cm
Package 1 Width	7.700 cm
Package 1 Length	9.700 cm
Package 1 Weight	200.000 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	30

Package 2 Height	20.500 cm
Package 2 Width	31.100 cm
Package 2 Length	42.000 cm
Package 2 Weight	6.382 kg

Contractual warranty

Warranty	12 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

China Rohs Regulation [China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure [Product Environmental Profile](#)

Weee The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Circularity Profile [End of Life Information](#)