# **Product datasheet**

Specifications





(!) Discontinued

# mini Kaedra - for modular device -1 openings - 6 modules

13977

() Discontinued on: 01-Nov-2020

#### Main

Range	Mureva	
Product Name	Mureva Enclosure	
Product Or Component Type	Weatherproof enclosure	
Enclosure Type	Mini enclosure for modular device	
Mounting Plate Description	Slotted	

### Complementary

Enclosure Mounting	Surface
9 Mm Pitches	12
Number Of 18 Mm Modules Per Row	6
Total Number Of 18 Mm Modules	6
Number Of Horizontal Rows	1
Electrical Insulation Class	Double insulation Class II
Provided Equipment	1 marking kit
Type Of Front Cover	Transparent
Power Dissipation In W	11 W
[In] Rated Current	63 A
Type Of Rail	DIN
Number Of Pre-Cutouts Pg Iso	3
Locking Options Description	Optional keylock
Enclosure Material	Self-extinguishing polymer
Width	159 mm
Height	200 mm
Depth	112 mm
Internal Depth	56 mm
Colour	Door: transparent green Enclosure: light grey (RAL 7035)

## Environment

Standards	IEC 60695-2-1 IEC 60670 IEC 61439-3 EN 50262	
Fire Resistance	650 °C conforming to IEC 60695-2-1	
Ip Degree Of Protection	IP65 conforming to IEC 60529	
Ik Degree Of Protection	IK09 conforming to EN 50102	
Environmental Characteristics (Uv)	UV resistant: class 3 conforming to ISO 4582:2010 Ultraviolet degradation test conforming to ISO 4892-2:2013	
Overvoltage Category	Category	
Ambient Air Temperature For Operation	-2560 °C	

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.15 cm
Package 1 Width	16 cm
Package 1 Length	20 cm
Package 1 Weight	515 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	7
Package 2 Height	34 cm
Package 2 Width	22 cm
Package 2 Length	41 cm
Package 2 Weight	4.015 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	168
Package 3 Height	80 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	108.36 kg

#### **Contractual warranty**

Warranty

18 months

### Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Lower Impact Materials Transparency RoHS/REACh

#### **Resource performance**

Minimum Percentage Of Recycled 25 Plastic Content

#### Well-being performance

Rohs Exemption Information	Yes
Halogen Free Product	

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations