



Auxiliary fault contact, Acti9 Vigi NG125, 1 SDV 1NO, 250VAC (0.1A to 1A)

19058

Main

Range Of Product	Acti9
Product Or Component Type	Fault contact
Device Short Name	SDV NO
Signal Contacts Composition	1 NO
[In] Rated Current	AC-14 0.11 A at 250 V, AC 50/60 Hz
9 Mm Pitches	1

Complementary

•	
[Ui] Rated Insulation Voltage	690 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	8 kV
Mounting Mode	Plug-on
Mounting Location	Upstream
Height	36 mm
Width	8.8 mm
Depth	34.64 mm
Electrical Durability	10000 cycles
Connections - Terminals	Plate terminal1 cable(s) 0.52.5 mm² - rigid Plate terminal1 cable(s) 0.51.5 mm² - flexible Plate terminal1 cable(s) 0.51.5 mm² - flexible with ferrule Plate terminal2 cable(s) 2.5 mm² - rigid Plate terminal2 cable(s) 2.5 mm² - flexible Plate terminal2 cable(s) 1.5 mm² - flexible Plate terminal2 cable(s) 1.5 mm² - flexible with ferrule
Wire Stripping Length	10 mm
Tightening Torque	1 N.m

Environment

Pollution Degree	3
Tropicalisation	2
Ambient Air Temperature For Operation	-2560 °C
Ambient Air Temperature For Storage	-4085 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Package 1 Height	2.5 cm
Package 1 Width	8 cm
Package 1 Length	10.6 cm
Package 1 Weight	35 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	9
Package 2 Height	11.5 cm
Package 2 Width	8.5 cm
Package 2 Length	23.7 cm
Package 2 Weight	378 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	81
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	3.889 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins