

Product datasheet

Specifications



103 x 225 mm plate - for 65 x 65 outlet or pushbuttons

13143

⚠ Discontinued on: 20-Nov-2023

⚠ Discontinued

Main

Range Of Product	Kaedra
Product Or Component Type	Plate
Type Of Front Plate	With cut-out
Accessory / Separate Part Type	Installation accessories
Socket Dimensions Compatible	1 gang 65 x 65 mm of socket-outlet

Complementary

Enclosure Material	Housing: self-extinguishing polymer
Net Weight	0.188 kg
Base Dimension	103 x 225 mm
Width	103 mm
Height	225 mm
Colour	Grey (RAL 7035)

Environment

Standards	IEC 60309-1 IEC 60309-2
Fire Resistance	650 °C conforming to IEC 60695-2-11
Ip Degree Of Protection	IP65 conforming to IEC 60529
Ik Degree Of Protection	IK09 conforming to IEC 62262

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.6 cm
Package 1 Width	12.3 cm
Package 1 Length	24.2 cm
Package 1 Weight	148 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	12.2 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Width	21.6 cm
Package 2 Length	27.2 cm
Package 2 Weight	1.33 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	24
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	4.477 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability





Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)