Product datasheet

Specifications





Acti 9 - low level auxiliary contact OF+SD - for C60, C120, C60H-DC, DPN, ID

A9N26899

Main

Range Of Product	Acti9	
Product Or Component Type	OC and fault contact	
Device Short Name	OF+SD 24	
Device Application	For Smartlink interface	
Signal Contacts Composition	1 NO + 1 NC	
[In] Rated Current	Current DC-12 2100 mA at 24 V, DC +/- 20 %	
9 Mm Pitches	1	

Complementary

[Ui] Rated Insulation Voltage	500 V conforming to IEC 60664-1	
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60664-1	
Local Signalling	Mechanical indicator	
Mounting Mode	Fixed	
Mounting Support	DIN rail	
Comb Busbar And Distribution Block Compatibility	Bottom: YES	
Height	85.5 mm	
Width	9 mm	
Depth	73.5 mm	
Net Weight	28 g	
Colour	White	
Electrical Durability	20000 cycles conforming to IEC 60947-5-4	
Connections - Terminals	Spring-loaded terminal Ti24 (top) 1 cable(s) 0.51.5 mm² - rigid Spring-loaded terminal Ti24 (top) 1 cable(s) 0.51.5 mm² - flexible	
Wire Stripping Length	10 mm	

Environment

Standards	IEC 60947-5-4 IEC 60947-5-1	
Quality Labels	CE	
Pollution Degree	2 conforming to IEC 60664-1	
Overvoltage Category	III	
Tropicalisation	2 conforming to IEC 60947-5-1	

Relative Humidity	93 % at 40 °C
Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-4085 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8 cm
Package 1 Width	2 cm
Package 1 Length	9.5 cm
Package 1 Weight	36 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	8.7 cm
Package 2 Width	10 cm
Package 2 Length	26.5 cm
Package 2 Weight	487 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	108
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	4.871 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
9	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information