Product datasheet





Acti 9 - Auxiliary contact OC plus 1 SD and OF ac dc

A9N26929

! To be discontinued on: 01-Jun-2024

① Discontinued

Main

Range Of Product	Acti9
Product Or Component Type	Double OC or fault contact
Device Short Name	OF and OF or OF and SD
Signal Contacts Composition	2 C/O
[In] Rated Current	DC-12 1 A at 130 V, DC DC-12 2 A at 48 V, DC DC-12 6 A at 24 V, DC AC-12 3 A at 415 V, AC 50/60 Hz AC-12 6 A at 240 V, AC 50/60 Hz
9 Mm Pitches	1

Complementary

Mounting Mode	Fixed
Mounting Support	DIN rail
Comb Busbar And Distribution Block Compatibility	NO
Height	90 mm
Width	9 mm
Depth	73.5 mm
Net Weight	38 g
Colour	White
Connections - Terminals	Screw clamp terminal (top and bottom) 2 cable(s) 1.5 mm² - flexible Screw clamp terminal (top and bottom) 1 cable(s) 0.52.5 mm² - rigid Screw clamp terminal (top and bottom) 2 cable(s) 1.5 mm² - flexible with ferrule
Wire Stripping Length	9 mm
Tightening Torque	1 N.m

Environment

Standards	EN/IEC 60947-5-1	
Product Certifications	ASTA ASEFA LCIE KEMA	
Ip Degree Of Protection	IP20 conforming to EN/IEC 60947-5-1	
Pollution Degree	3 conforming to EN/IEC 60947-5-1	
Tropicalisation	2 conforming to EN/IEC 60947-5-1	

Life Is On Schneider 25-Apr-2024

Ambient Air Temperature For Operation	-2550 °C
Ambient Air Temperature For Storage	-4085 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.2 cm
Package 1 Width	8 cm
Package 1 Length	9.2 cm
Package 1 Weight	46 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	8.7 cm
Package 2 Width	10 cm
Package 2 Length	26.5 cm
Package 2 Weight	609 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	108
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	5.94 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
9	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information