# **Product datasheet**

Specifications





# Plug outlet, Linergy HK, 3P, 16A, 2 points, 2.5mm<sup>2</sup>, cable length 200

AK5PC13

#### Main

Range	Linergy
Product Name	НК
Product Or Component Type	Plug outlet
Poles Description	3P
[Ith] Conventional Free Air Thermal Current	16 A
I <sup>2</sup> T On Activation	100000 A².s
Number Of Points	2
Number Of Cables	3 cable(s) 2.5 mm <sup>2</sup>
Cable Length	0.2 m
Quantity Per Set	Set of 6

## Complementary

[Ui] Rated Insulation Voltage	600 V conforming to CSA 600 V conforming to UL 690 V conforming to IEC 60439-1
Peak Current	25 kA
Width	36 mm
Height	46 mm
Depth	38 mm
Net Weight	0.04 kg

#### Environment

Standards	IEC 60439
Product Certifications	DNV LROS (Lloyds register of shipping) UL CSA

### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.500 cm
Package 1 Width	9.000 cm
Package 1 Length	12.000 cm

Package 1 Weight	44.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	12.700 cm
Package 2 Width	13.000 cm
Package 2 Length	15.000 cm
Package 2 Weight	325.000 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	96
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	5.937 kg

# **Contractual warranty**

Warranty

18 months

# Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations