Product datasheet

Specifications





PratiKa wander plug - 90° angled -32 A - 2P + E - 200...250 V AC -IP67

81766

Discontinued on: 01-Nov-2020

(!) Discontinued

Main

Range	Mureva
Product Or Component Type	Wander plug
Device Short Name	Mureva plug
Plug, Socket Category	Low voltage
Poles Description	2P + E
Network Type	AC
Outlet Standard	Industrial

Complementary

· · · · · · · · · · · · · · · · · ·	
Plug, Socket, Control Station Shape	90° angled
[In] Rated Current	32 A
[Ue] Rated Operational Voltage	200250 V
Network Frequency	50/60 Hz
Ground Lug Clockwise Position	6 h
Plug, Socket Material	Housing: self-extinguishing engineering polymer
Contacts Material	Pins: nickel plated brass
Connections - Terminals	Captive screws
Cable Cross Section	2.510 mm ²
Cable Outer Diameter	11.521 mm
Cable Entry	Cable gland
Thread Type	Pg 21
Net Weight	0.258 kg
Height	141 mm
Width	113 mm
Depth	113 mm
Colour	Grey (RAL 7035)
Voltage Colour	Blue

Environment

Standards

IEC 60309-1 IEC 60309-2

Ip Degree Of Protection	IP67 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to EN 62262
Fire Resistance	850 °C conforming to IEC 60695-2-11
Relative Humidity	50 % at 40 °C 70 % at 30 °C 90 % at 20 °C
Operating Altitude	2000 m
Ambient Air Temperature For Operation	35 °C (86400 s) -25…40 °C

Packing Units

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	14 cm
Package 1 Width	10 cm
Package 1 Length	9 cm
Package 1 Weight	236 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	16 cm
Package 2 Width	21.5 cm
Package 2 Length	27 cm
Package 2 Weight	1.569 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	12
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	3.625 kg

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Rohs Exemption Information

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations