Product datasheet

Specification





Acti 9 - MINt - silent electronic timer - adjustable from 0.5 to 60 minutes

CCT15234

Main

Range Of Product	Acti9
Product Name	Acti9 MIN
Device Short Name	MINt
Product Or Component Type	Silent electronic timer
Product Compatibility	Mechanical compatibility with electrical comb busbars
Function Available	Impulse relay Switch-off warning
Colour Tint	White (RAL 9003)

Complementary

Device Application	Building
Load Type	Fluocompact lampconventional ballast 1500 VA
	Fluorescent lamp 22 x electronic ballast 23 W
	230 V AC halogen lamp 3600 W
	230 V AC incandescent lamp 3600 W
	Fluorescent lamp 24 x electronic ballast 15 W
	Fluorescent lamp 27 x electronic ballast 11 W
	Fluorescent lamp 34 x electronic ballast 7 W
	Dual mounted fluorescent tubeconventional ballast 3600 VA
	Fluorescent tubeelectronic ballast 1000 VA
	Non-corrected fluorescent tubeconventional ballast 3600 VA
	Parallel-corrected fluorescent tubeconventional ballast 1200 VA
	Serial-corrected fluorescent tubeconventional ballast 3600 VA
Power Consumption In Va	6 VA
Maximum Switching Current	16 A - 230 V AC pf = 1
[Ue] Rated Operational Voltage	230 V AC +10 % -15 % at 50/60 Hz
Time Delay	Adjustable from 0.5 to 20 minutes
Mounting Support	DIN rail
9 Mm Pitches	2
Connections - Terminals	Screw terminals - <= 6 mm²
Electrical Insulation Class	Class II
Width	18 mm
Height	89 mm
Depth	66 mm
Net Weight	76 g

Environment

Ambient Air Temperature For Operation	-2550 °C
Ip Degree Of Protection	IP20 B

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.2 cm
Package 1 Width	2.2 cm
Package 1 Length	10.5 cm
Package 1 Weight	101 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	130
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	13.604 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information