Product datasheet

Specifications





Cable end, Linergy TR cable ends, twin conductor, red, 1mmÂ², medium size, 5 sets of 50

AZ5DE010

Main

Range Of Product	Linergy
Product Or Component Type	Cable end
Cable End Size	Medium
Standards	NF C 63-023
Type Of Packing	Dispenser pack
Quantity Per Set	5 sets of 100
Cable Cross Section	1 mm ²

Complementary

Cable End Type	Twin conductor
Additional Information	Without marker tag holder
Colour	Red
Bezel Material	Halogen-free plastic
Tube Material	Copper conforming to ISO 1337
Number Of Cables	2
Awg Gauge	AWG 18
Bezel Size	Ø 3.4 x 5.4 mm
Tube Diameter	2.25 mm
Length	15 mm
Tube Length	8 mm
Net Weight	0.14 kg

Environment

Product Certifications	cCSAus
Ambient Air Temperature For Operation	-20105 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.400 cm
Package 1 Width	0.400 cm
Package 1 Length	1.400 cm

Package 1 Weight	0.200 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	500
Package 2 Height	13.100 cm
Package 2 Width	7.000 cm
Package 2 Length	12.500 cm
Package 2 Weight	139.000 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	20000
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	6.399 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free
Halogen Free Plastic Parts Product

Certifications & Standards

Circularity Profile	No need of specific recycling operations
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Reach Regulation	REACh Declaration