Product datasheet

Specifications





AvatarOn, push button for doorbell, 10A, 250V, LED, Light Wood

E8331BPDMW_LW_G8

! Discontinued on: 03-Jul-2023

! Discontinued

Main

Product Or Component Type	Push-button
Device Application	Doorbell
Colour Tint	Light wood
Colour Tint	Light wood

Complementary

•	
Device Presentation	Complete product
Rated Current	10 A at 250 V AC 50/60 Hz
Number Of Gangs	1 gang
Number Of Rocker	1
Clamping Connection Capacity	3 x 2.5 mm² for solid cable(s)
	3 x 2.5 mm² for stranded cable(s)
	4 x 1.5 mm² for solid cable(s)
	4 x 1.5 mm² for stranded cable(s)
Connections - Terminals	Brass terminal
Local Signalling	LED indicator, LED
Material	Polycarbonate: grid plate
	Polycarbonate: base
	Polycarbonate: dolly
	Polycarbonate: frame
	Polycarbonate + GF 20 %: actuator
Marking	DO NOT DISTURB
-	Clean up symbol
	Bell symbol
Device Mounting	Surface
	Flush

Environment

Ip Degree Of Protection	IP20
Maximum Ambient Air Temperature For Operation	35 °C
Relative Humidity	095 %
Standards	GB 16915.1 IS 3854

Packing Units

Unit Type Of Package 1 PCE

Number Of Units In Package 1	1
Package 1 Height	3.4 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	114.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	9.5 cm
Package 2 Width	19.0 cm
Package 2 Length	19.5 cm
Package 2 Weight	1.14 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations