# **Product datasheet**

Specifications





# AvatarOn, push button for doorbell, 10A, 250V, LED, Wine Gold

E8331BPDMW\_WG\_G8

#### Main

Product Or Component Type	Push-button
Device Application	Doorbell
Colour Tint	Wine gold
Colour Tint	Wine gold

## Complementary

· · · · · · · · · · · · · · · · · ·	
Device Presentation	Complete product
Rated Current	10 A at 250 V AC 50/60 Hz
Number Of Gangs	1 gang
Number Of Rocker	1
Clamping Connection Capacity	3 x 2.5 mm <sup>2</sup> for solid cable(s) 3 x 2.5 mm <sup>2</sup> for stranded cable(s) 4 x 1.5 mm <sup>2</sup> for solid cable(s) 4 x 1.5 mm <sup>2</sup> for stranded cable(s)
Connections - Terminals	Brass terminal
Local Signalling	LED indicator, LED
Material	Polycarbonate: grid plate Polycarbonate: base Polycarbonate: dolly Polycarbonate: frame Polycarbonate + GF 20 %: actuator
Marking	DO NOT DISTURB Clean up symbol Bell symbol
Device Mounting	Surface Flush

#### Environment

Ip Degree Of Protection	IP20
Maximum Ambient Air Temperature For Operation	35 °C
Relative Humidity	095 %
Standards	GB 16915.1 IS 3854

### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

3.4 cm
8.6 cm
8.6 cm
114.0 g
BB1
10
9.5 cm
19.0 cm
19.5 cm
1.14 kg
CAR
60
21.0 cm
30.0 cm
39.5 cm
6.84 kg

# Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations