Product datasheet

Specifications





Fire detection panel, Esmi Sense FDP252

FFS00703920GB

Main

Range Of Product	Esmi fire detection panels
Product Or Component Type	Control panel
Number Of Batteries	2 x 12 V 17 Ah
Colour	Cover: light grey (NCS S 1005-R80B) Frame: dark grey (NCS S 7502-B)
Maximum Allowed Current Consumption	1.0 A at 24 V DC standby 4.8 A at 24 V DC alarm

Complementary

oomprementary	
Mains Supply Power	165 VA
Mains Supply Voltage	230 V AC +/- 10 % at 5060 Hz
Operating Voltage Range	1930 V DC
Device Composition	cover in plastic frame in sheet steel/plastic back frame in sheet steel
Height	580.0 mm
Width	430.0 mm
Depth	142.0 mm
Product Weight	10.6 kg without batteries
Addressable Loop Controller	ALC2/SLC
Number Of Loops	8 addressable
Number Of Addresses	0159 addressable detectors and call points for SLC 0159 other modules for SLC 0126 addressable devices for ALC
Optional Circuit Board Slots	5 optional circuit board
Product Compatibility	Fireman's panel FMP Protocol repeater REP/REPX-OB Delay alarm panel DAP Logical controller MCO/MCOX-OB LED panels for fire zones ZLPX

Environment

Standards	EN 54-2 EN 54-4
Relative Humidity	094 % non-condensing
Ambient Air Temperature For Operation	540 °C
Ambient Air Temperature For Storage	050 °C

Ip Degree Of Protection	IP30	
Packing Units		
Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Weight	10600 g	

Contractual warranty

Warranty

24 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information