Product datasheet

Specifications





AvatarOn, push button for doorbell, 10A, 250V, Wood

E8331BPL1_WD_G8

Main

Product Or Component Type	Push-button
Device Application	Doorbell
Colour Tint	Wood
Colour Tint	Wood

Complementary

· · · · · · · · · · · · · · · · · ·		
Device Presentation	Complete product	
Rated Current	10 A at 250 V AC 50/60 Hz 1 gang	
Number Of Gangs		
Number Of Rocker	1	
Clamping Connection Capacity	3 x 2.5 mm ² for solid cable(s)	
	3 x 2.5 mm ² for stranded cable(s)	
	4 x 1.5 mm ² for solid cable(s)	
	4 x 1.5 mm ² for stranded cable(s)	
Connections - Terminals	Brass terminal	
Material	Polycarbonate: grid plate	
	Polycarbonate: base	
	Polycarbonate: dolly	
	Polycarbonate: frame	
	Polycarbonate + GF 20 %: actuator	
Marking	Bell symbol	
Device Mounting	Surface	
	Flush	
Width	86 mm	
Height	86 mm	

Environment

Ip Degree Of Protection	IP20	
Maximum Ambient Air Temperature For Operation	45 °C	
Operating Altitude	2000 m	
Relative Humidity	095 %	
Environmental Characteristic	UV resistant	
Standards	MS IEC 60669-1 SS 227-1 BS EN 60669-1 IEC 60669-1 IS 3854	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.4 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	81.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	9.5 cm
Package 2 Width	19.0 cm
Package 2 Length	19.5 cm
Package 2 Weight	810.0 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	60
Package 3 Height	21.0 cm
Package 3 Width	30.0 cm
Package 3 Length	39.5 cm
Package 3 Weight	4.86 kg

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations