Product datasheet

Specification





End feed unit, Canalis KSA400, aluminium, 400A, right or left mounting, without line protection, 3L+N+PE, white RAL9001

KSA400AB4

Main

Range Of Product	Canalis
Product Name	KS
Device Short Name	KSA
Product Compatibility	Canalis KSA busbar trunking 400 A
Offer Type	Classic Rising main
Product Or Component Type	Feed unit
Conductors Material	Aluminium
[le] Rated Operational Current	400 A
[Ue] Rated Operational Voltage	230690 V
Number Of Circuits	1
Busbar Trunking Polarity	3L + N + PE
Protection Type	Without protection
Control Type	Without
Colour	White (RAL 9001)

Complementary

Provided Equipment	End cover
Mounting Location	Right Left
Mounting Mode	By screws
Mounting Support	Busbar
Body Material	Metal
Connections - Terminals	Lug for 300 mm² rigid Lug for 300 mm² flexible
Width	501 mm
Depth	213.5 mm
Height	348 mm
Net Weight	11.2 kg
Standards	IEC 61439-1 IEC 61439-6

Environment

Ip Degree Of Protection	IP55 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to IEC 62262

Packing Units

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	25.500 cm
Package 1 Width	42.000 cm
Package 1 Length	44.000 cm
Package 1 Weight	11.750 kg
Unit Type Of Package 2	PAL
Number Of Units In Package 2	6
Package 2 Height	91.000 cm
Package 2 Width	60.000 cm
Package 2 Length	84.000 cm
Package 2 Weight	77.500 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
⊘	Halogen Free Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations

KSA400AB4

Dimensions Drawings

Dimensions

