



Microperforated mounting plate H1200xW1000 w/holes diam 3,6mm on 12,5mm pitch

NSYMF1210

! Discontinued on: 01-Nov-2020

! Discontinued

Main

Range	Spacial	
Accessory / Separate Part Category	Mounting accessory	
Product Or Component Type	Mounting plate	
Device Application	Multi-purpose	
Enclosure Nominal Dimensions	- H: 1000 mm W: 1200 mm - H: 1200 mm W: 1000 mm	
Mounting Location	Direct fixing on backstuds Step slide	
Mounting Plate Description	Microperforated	
Range Compatibility	Compatibility Spacial Spacial S3D Spacial Spacial CRN Spacial Spacial S3X	
Quantity Per Set	Set of 1	
Material	Galvanised steel	

Complementary

Fixing Mode	Screwed on backstuds - screw type M8 By fixing element
Permanent Permissible Load	180 kg
Height	1165 mm
Width	965 mm
Depth	125 mm
Thickness	2.5 mm
Net Weight	21.551 kg
Variant Particularity	Installation in enclosures with inverted dimensions

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.5 cm
Package 1 Width	95 cm
Package 1 Length	115 cm
Package 1 Weight	20.8 kg

Unit Type Of Package 2	PAM
Number Of Units In Package 2	25
Package 2 Height	64 cm
Package 2 Width	100 cm
Package 2 Length	120 cm
Package 2 Weight	548 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations