Product datasheet

Specifications





drilled front plate - XAP-E - metal - 5 horizontal openings

XAPE305

Main

Range Of Product	Harmony XAP		
Product Or Component Type	Front plate with fixing screws		
Device Short Name	XAPE		
Product Destination	For Ø 22 mm control and signalling units		
Product Front Plate Size	72 x 204 mm		
Number Of Cut-Out	5 cut-outs		
Material	Anodised aluminium		
Device Mounting	Flush		
Ip Degree Of Protection	IP65 conforming to IEC 60529 IP657 conforming to NF C 20-010		
Resistance To Chemical Agents	Good resistant to acetone Good resistant to alcohols Good resistant to chloride and fluoride solvents Good resistant to diluted mineral acids Good resistant to oils and petrol Good resistant to organic acids Good resistant to salts		

Complementary

Net Weight	0.135 kg		
Environment			
Protective Treatment	TH TC		

	тс	
Ambient Air Temperature For Storage	-4070 °C	
Ambient Air Temperature For Operation	-2570 °C	
Overvoltage Category	Oltage Category Class I conforming to IEC 60536 Class I conforming to NF C 20-030	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.8 cm
Package 1 Width	13.9 cm
Package 1 Length	23.0 cm
Package 1 Weight	160.0 g

Unit Type Of Package 2	S02
Number Of Units In Package 2	21
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.669 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Product datasheet


Dimensions Drawings

Dimensions and Fixing

Below drawing shows a front plate with 4 cut-outs. Refer to the product characteristics to get the number of cut-outs.







b		b1		Н	
mm	in.	mm	in.	mm	in.
204	8.03	176	6.93	188	7.40