


Gaminio duomenų lentelė

Specifikacijos

k1 contact block



K1S4

Main

Range of product	Harmony K
Product or component type	Cam switch body
Component name	K1
[I _{th}] conventional free air thermal current	12 A
Sub-assembly composition	Contact blocks + fixing plate
Cam switch function	Switch
Mounting location	Front
Fixing mode	Ø 22 mm hole
Bezel material	Plastic

Complementary

[U _i] rated insulation voltage	690 V 3)IEC 60947-1
[I _{the}] conventional enclosed thermal current	10 A
Rated operational power in W	10500 W AC-21, 500 - 660 V 3 phases IEC 947-3
[I _e] rated operational current AC	1 A 500 V AC-15 IEC 947-5-1
Electrical durability	1000000 cycles AC-15
Maximum operating rate	2,5 cyc/mn AC-21
Short-circuit current	10000 A
Short-circuit protection	20 A cartridge fuse gG
[U _{imp}] rated impulse withstand voltage	4 kV in isolating function
Contact operation	Slow-break
Positive opening	With
Electrical connection	Captive screw clamp terminals flexible 2 x 1.5 mm ²
Mechanical durability	1000000 cycles

Environment

Standards	CENELEC EN 50013
-----------	------------------

Product certifications	CSA 240 V 1 hp 1 phase
Protective treatment	TC
Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-40...70 °C
Shock resistance	30 gn IEC 68-2-27
Vibration resistance	5 gn 10...150 Hz)IEC 68-2-6
Overvoltage category	Class II IEC 536
IP degree of protection	IP40 IEC 529

Pakavimo vienetai

Pirmos pakuotės vieneto tipas	PCE
Vienetų skaičius 1 pakuotėje	1
1-os pakuotės aukštis	8,0 cm
1-os pakuotės plotis	6,5 cm
1-os pakuotės ilgis	6,5 cm
1-os pakuotės svoris	114,0 g
Antros pakuotės vieneto tipas	S01
Vienetų skaičius 2 pakuotėje	16
2-os pakuotės aukštis	15,0 cm
Package 2 Width	15,0 cm
2-os pakuotės ilgis	40,0 cm
2-os pakuotės svoris	2,069 kg

Offer Sustainability

REACH direktyva	REACH deklaracija
REACH be SVHC	Taip
ES RoHS direktyva	Aktyvus laikymasis (gaminys nepatenka į ES RoHS teisinę aprėptį) ES RoHS deklaracija
Be sunkių toksiškų metalų	Taip
Be gyvsidabrio	Taip
Kinijos RoHS direktyva	Kinijos RoHS deklaracija
RoHS išimčių informacija	Taip

Rekomenduojamas (-i) pakeitimas (-ai)